





3 Points of Spatoilet...

Enema Wash

Soft but powerful water wash for added cleansing benefit



Fits most 1 and 2 piece toiltes. Sleek-Low profile-Contoured design

Instant Heating

Enjoy efficient and continuous warm water with energy saving

Features of Spatoilet...

Bubble Wash

Aerated water wash aids cleaning

Child Settings

Adjust nozzle position and water pressure for children

Pulse

Pulse wash repeatedly cycles from weak to strong

Massage

Nozzle moves back and forth for massage effect

Adjustable Nozzle Position

Users can adjust nozzle position to desired setting

Seat Sensor

User must be sitting position to desired setting

Seat temperature can be adjusted

by 4 levels. (Room temp/93°F/100°F/107°F) (Room temp/34°C/38°C/42°C)

User Preset

User presets and stores the memory for control setting for 4 users

Self-Diagnosis

Self diagnosis function contiuously monitors operation

Learning Energy Save

Energy saving computer function learns through weekly use patterns to save energy

Self-Cleaning

To wash and maintain clean nozzle that operates before and after every use

Detachable Main Body

It is easy to install and detach for cleaning or moving

Low Noise Motor Pump

Provides quiet and constant water pressure for effective washing

Dry After using the bidet, the user has the

option to dry washed area

Deodorization

A small fan circulates air through a carbon filter improving the air quality

Remote Control

All operating functions are controlled from a wireless remote control with LCG



Seat Temperature









Specifications

	Spatoilet	CE (EUROPE)	UL (USA)			
	Diamond	Diamond	Diamond			
	Power Supply	220V - 240V / 50Hz	AC120V / 60Hz			
	Power Consumption	1670W	1270W			
General	Power Cord Length	1.8m	4 ft.			
	Water Pressure	0.75 - 7.5kgf/cm2	10.7 - 106.6 psi			
	Dimension	406x496x145	16.0x19.5x5.7			
	Weight	4.6kg	10.1lb			
	Power Consumption	1600W	1200W			
	Wash Volume	0.7 l / min.	0.16gal / min.			
	Bidet Volume	0.7 l / min.	0.16gal / min.			
	Enema Volume	0.7 l / min.	0.16gal / min.			
Wash	Nozzle Position Control	5 Steps	5 Steps			
	Nozzle Pressure Control	5 Steps	5 Steps			
	Water Temp. Control	4 Steps	4 Steps			
	Safety Device	Temp. Sensor, Bimetal, Fuse	Temp. Sensor, Bimetal, Fuse			
	Power Consumption	250W	250W			
Dry	Dry Temp. Control	5 Steps	5 Steps			
	Safety Device	Bimetal, Fuse	Bimetal, Fuse			
	Power Consumption	55W	55W			
114101	Seat Temp. Control	4 Steps	4 Steps			
Heated Seat	Safety Device	Temp. Sensor, Fuse	Temp. Sensor, Fuse			
	Seat Sensor	Body Sensor	Body Sensor			

Functions

Model	Massage & Pulse	Self Cleaning			Water & Temp Control	Safety Device	Soft Closing	Learning Energy Save	Dry	Deodorization	Remote Control	User Preset
Diamond	•	•	•	•	•	•	•	•	•	•	•	•



Theorema by Tel: (+31) (0)900-SPATOILET® (772864538)

Dreef 9-A Tel: (+31) (0)72-5629269
1861 TX Bergen NH Email: info@spatoilet.com
Nederland Website: www.spatoilet.com

